

### SPECIFICATIONS

**Housing:** 20 gauge C.R.S. die-formed and welded construction with adjustable uni-lug levelers for ceiling thickness of  $\frac{3}{4}$ " minimum to 3" maximum. Finished matte black. See finish note.

**Reflector:** One piece hydro-formed aluminum finished bright dipped anodized.

**Doorframe:** Removable one piece die-formed stainless steel with continuous piano hinge, captive allen head fasteners. Gasketed with black closed cell neoprene to eliminate any light leaks. Finished satin brushed.

**Filters:** Specification grade safelight filters (select proper filter for required application).

**Diffuser:** Prismatic glass lens.

**Thermal Device:** Automatic resetting heat sensitive device for non-ic installations. Protects fixture from overheating if insulation covers fixture.

**Lamp Holder:** High heat porcelain, medium base.

**Lamps:** 15 Watt A15 incandescent for filter compartments. 200 Watt A-23 incandescent for general lighting compartment (by others).

**Finish:** All painted parts are washed in alkaline solution, rinsed in an iron phosphate, baked dry, then painted with a TGIC polyester powder coating electrostatic applied and baked.


**Labels:** ETL, CETL listed, I.B.E.W. labeled.

**Fixture Warranty:** The fixture mechanics are guaranteed to be free from defective material and workmanship, under normal installation and operating conditions, for five years from date of shipment from the factory. See General Terms and Conditions.



**SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE**

### DIMENSIONS



3254 North Kilbourn Avenue Chicago, Illinois 60641-4505  
Phone: 773-427-7000 Fax: 800-217-1260 [www.escolighting.com](http://www.escolighting.com)

**A Woman-Owned Business**

**Established 1975**



**HOW TO ORDER**

Use the table below to choose the Kodak filter of your choice and suffix the catalog number with the Esco filter number.

**EXAMPLE: R3EOC** = Recessed 3 light darkroom fixture with Kodak light amber filters.

Esco Filter Number	Kodak Filter Designation	Color	Usage
<b>EOC</b>	OC	Light Amber	Contact and enlarging papers.
<b>E-1</b>	1	Red	Blue sensitive materials Kodagraph projection paper and most phototypesetting materials.
<b>E-1A</b>	1A	Light Red	Slow orthochromatic materials.
<b>E-3</b>	3	Dark Green	Some panchromatic materials.
<b>E-7B</b>	7B	Green	Black and white infrared materials, some panchromatic materials, except Kodak high-speed infrared films.
<b>E-10</b>	10	Dark Amber	Color negative papers, color slide and print materials, panchromatic black and white papers.
<b>E-13</b>	13	Amber	Color negative papers, panchromatic black and white papers
<b>E-GBX-2</b>	GBX-2	Brown	Most blue sensitive x-ray films, most green sensitive medical x-ray films.



3254 North Kilbourn Avenue Chicago, Illinois 60641-4505  
 Phone: 773-427-7000 Fax: 800-217-1260 [www.escolighting.com](http://www.escolighting.com)  
**A Woman-Owned Business**  
 Established 1975

